 <p>15 Rue des Frères Lumière – BP 136 78374 PLAISIR FRANCE</p> <p>Pho : +33(0)1.30.80.81.98 Fax : +33(0)1.30.80.81.99 WEB : www.babbco.fr E-MAIL : sherwinbabbco@orange.fr</p>	<p>TECHNICAL DATA SHEET</p>	<p>Ref : TDS/HM-430</p> <p>Page : 1/2</p> <p>Rev : 2 Date : 11/09</p>
--	--	--

FLUORESCENT PENETRANT HM-430



MANUFACTURER: SHERWIN Inc (USA) / NDT-Europa (ND)

DESCRIPTION / APPLICATION(S):

Level 3 water washable fluorescent penetrant designed for detecting surface defects.

.Companion product(s):

DR 60, DR 62 removers

N 120 degreaser / N 106 A,

D 100, D90G developer

R 62 quick-drying developer

SPECIFICATION(S) / STANDARD(S):

SAE-AMS 2644-QPL 2644-1

Type 1 Method A Level III

RCCM (EDF) code-compliant

Mc DONNELL/DOUGLAS: grade 3

ALLISON: level 2

SNECMA: sensitivity S2

AIRBUS-EADS: type I, method A, level III


ROLLS ROYCE: RPS 702 –F1B TSD 594 – 213 standard

BOEING, LOOKHEED, GENERAL ELECTRIC: in accordance with AMS 2644 – QPL 2644-1

DASSAULT: type I, method A, level III

PHYSICO-CHEMICAL PROPERTIES:

- Aspect: green liquid
- Fluorescence: green-yellow
- Flash point: > 93°C. (200°F)
- Viscosity: 19 mm²/s ± 15 % at 40°C.
- Density: 0.9
- Water tolerance: > 5 %
- Performance: >75 % on a 10 µm sample
- Very low halogen and sulfur content
- Compatible with all metals and certain plastics.

 <p>15 Rue des Frères Lumière – BP 136 78374 PLAISIR FRANCE</p> <p>Pho : +33(0)1.30.80.81.98 Fax : +33(0)1.30.80.81.99 WEB : www.babbco.fr E-MAIL : sherwinbabbco@orange.fr</p>	<h1>TECHNICAL DATA SHEET</h1>	<p>Ref : TDS/HM-430</p> <p>Page : 2/2</p> <p>Rev : 2 Date : 11/09</p>
--	-----------------------------------	---

PACKAGING / SHIPPING / STORAGE:

- . **Packaging:** 1-, 5-, 10-liter canisters
60-liter drum
200-liter drum

. **Shipping / Handling: refer to MSDS**

- . **Storage / Lifespan:** keep away from moisture
Temperature limit : 0 to 50°C. (32° to 120°F)
Keep the packaging closed after taking out some of the product
Canister/Drum: 48 months

INSTRUCTIONS : (These describe the basic process, but they may need to be amended by the user to comply with applicable specifications and/or inspection criteria provided by the contracting agency).

- 1. Application** : Apply HM-430 only to clean, dry surfaces by spraying, flowing, brushing or dipping.
- 2. Dwell-Time** : A 10 minute dwell time is suggested, although in many cases five minutes will suffice. When particularly tight cracks are suspected, or the part is especially critical, the dwell time may be extended to 30 minutes, or longer.
- Do not soak the part.** To increase sensitivity, as well as conserve material, allow the penetrant to drain from the part surface back into the penetrant tank.
- 3. Removal** : Use a quick, ambient temperature water wash at tap pressure to rinse HM-430 from the part surface. To avoid washing entrapped penetrant from surface flaws, do not use high water pressures and temperatures, or prolonged washing and scrubbing.
- 4. Drying** : A recirculating oven set no higher than 160°F (71°C) is suggested. Leave part in oven just long enough to evaporate surface moisture. Drying is improved by using pressurized air to disperse and remove as much excess water as possible before placing part in oven.
- 5. Developing** : HM-430 is self developing. Nevertheless it is recommended to use a developer as listed above.
- 6. Inspection** : Inspect parts under appropriate UV-A radiation and dimmed visible light, in accordance with ISO 3059-2001 standard.

HEALTH AND SAFETY: refer to MSDS.

The figures provided in this datasheet are given in all good faith to our customers, out of the sole concern to inform them and help them in their research and verifications. There is no formal or implicit guarantee as to the use of this document.

Consequently, BABB CO may not be held liable for damages for any nature whatsoever arising from the publication of this document. Likewise, none of the information it contains should be construed as an authorization or recommendation to use products that may violate protected industrial property rights.